

Specifications and Models of Grinding Wheels for Ceramic Fuse Inserts



Overview

Paradigm wheels for insert radius and plunge form grinding are available for all common machine wheel sizes including 200mm, 250mm, 350mm, and 400mm diameters in 2A2 and 11A2 wheel shapes.

Key Takeaways

Ceramic fuse inserts are typically ground using high-performance ceramic or diamond grinding wheels with vitrified or resin bonds, available in various shapes, sizes, and grit levels for precision and durability. Types of Grinding Wheels1. Peripheral Grinding Wheels: Used for flat and cylindrical surfaces of ceramic inserts.

Bond types: resin ceramic bond, metal hybrid bond, or resin hybrid bond. Diameter range: 75 mm to 400 mm. Features: low grinding pressure, cool grinding, high stock removal, suitable for CNC creep feed grinding.

2. Cut-off Wheels: Steel body or continuous abrasive layer. Characteristics: free-cutting, thin wheels, wet or dry grinding.

Ideal for precise cutting of ceramic fuse inserts. 3. Profile and Pointed Wheels: For grooving, fluting, and shaping inserts.

High tool life, stable radii, and consistent quality.



Abrasive Materials

Ceramic Alumina (Al_2O_3): High toughness, suitable for hard ceramics and carbide inserts. Silicon Carbide (SiC): Needle-shaped grit, ideal for fine grinding of ceramics and high-alloy materials. Zirconia Alumina: Strong, wear-resistant, suitable for high-speed grinding.

Diamond or CB

N: For extremely hard ceramic or PCD/PCBN inserts, providing fast stock removal and long life.

Bond Types

Vitrified Bond: High precision, stable shape, suitable for high-speed grinding. Resin Bond: Cooler grinding, high stock removal, suitable for regrinding and CNC applications. Hybrid Bonds: Combine bite and cooling properties for aggressive yet controlled grinding.

Wheel Shapes and Sizes

Shapes: Parallel, cup, saucer, column, bowl, peach, trapezoid, concave (single/double-sided), cuboid, cone, and custom shapes. Diameter: 10 mm to 1500 mm depending on application. Grit Size: P36 to 3000, allowing coarse to ultra-fine finishes.

Colors: Grey, red, blue, pink, black, yellow, white, khaki, indicating different abrasive types or bonds.

Applications

Grinding of ceramic fuse inserts, carbide tools, PCD/PCBN inserts. Precision operations: coordinate grinding, profile grinding, double-sided face grinding, honing. Industries: automotive, aerospace, electronics, home appliances, hardware, and stone processing.

Key Considerations

Thermal Management: Ceramic grinding wheels generate heat; resin or hybrid bonds help reduce thermal stress. Brittleness: Ceramic wheels are hard but brittle; low-speed operation is recommended for safety. Custom Solutions: Many manufacturers offer custom-shaped wheels for specific insert geometries or high-precision requirements.

By selecting the appropriate abrasive type, bond, grit size, and wheel shape, manufacturers can achieve precise, efficient, and durable grinding of ceramic fuse inserts.

Article Content

How to Choose the Right Grinding Wheel for Machining Ceramic

As a professional manufacturer of superabrasives (Diamond and CBN grinding wheels), we know that selecting the precisely matched grinding wheel is the ultimate key to maximizing yield

Ceramic grinding wheel

Find your ceramic grinding wheel easily amongst the 26 products from the leading brands (METABO, FEMI, STUDER, ...) on DirectIndustry, the industry specialist

DIAMOND WHEELS FOR INSERT FORM GRINDING

Paradigm wheels for insert radius and plunge form grinding are available for all common machine wheel sizes including 200mm, 250mm, 350mm, and 400mm diameters in 2A2 and 11A2 wheel shapes.

DIAMOND WHEELS FOR INSERT PERIPHERY GRINDING

Prior to order entry, please contact your Norton representative for specification recommendations to ensure maximum grinding performance, quotations, and current lead-times.

Grinding Wheels for Ceramic | McMaster-Carr

Choose from our selection of grinding wheels for ceramic, including over 225 products in a wide range of styles and sizes. Same and Next Day Delivery.

Haefeli Diamantwerkzeugfabrik AG

Below you find the most common micro grinding drills, grinding pins and small grinding wheels that we manufacture. We have a broad range of grinding pins on

Diamond Grinding Wheels for Glass & Ceramics | ZYsuperhard

ZYsuperhard offers high-performance diamond grinding wheels (metal/resin bond) for optical glass, technical ceramics & more. Achieve precision, long life & custom solutions.

Superfinishing wheels

Our superfinishing tools (files, grinding stones and wheels) are available with 3 types of grain finish: fine, medium or coarse. These different finishes ensure that

Full text of "NEW"

Full text of "NEW" See other formats Word . the, > < br to of and a : " in you that i it he is was for - with) on (? his as this ; be at but not have had from will are they -- ! all by if him one your

Ceramic Grinding Wheels 101: Types, Functions, and

Looking for a ceramic grinding wheel? Find out everything you need to know about ceramic grinding wheels, including types, uses, and benefits, in this

A Comprehensive Guide to Grinding of Ceramics

Unlock the secrets of perfect ceramic grinding! Discover expert tips, techniques, and tools to take your grinding skills to the next level. Click now!

Abrasive Wheels Guide: Grinding Wheel Types and More

Abrasive wheels quickly remove material, shape workpieces and even cut through metal and stone. Learn about the types of abrasive wheels, including grinding wheels and cutting wheels,

SG (Sol Gel) Grinding Wheel

SG (Sol Gel) Grinding Wheel Grinding wheel made of ceramic abrasive with has a higher durability and longer life, which is 5-10 times than the grinding wheel

Grinding Wheel Grit Chart | Find the Perfect Match

Learn how to select the right grinding wheel with our complete grit chart. Compare wheel types, grit, grades, and bonds for stainless steel, cast iron,

Grinding and Cutting Wheels Guide

Grinding and Cutoff Wheels Technical Information: Types and Selection Grinding and cutoff wheels are used in industrial applications to remove, shape, and finish materials. Available in various sizes,

MACHINING/FINISHING: Diamond Wheel Grinding 101

The functional reliability of an advanced ceramic component is greatly influenced by the machining process, especially in diamond wheel grinding. Understanding and controlling the grinding

Ceramic Wall Tiles Wheel

Metal bond SP1001 & SP1002 sizing wheels are prior to focus on the cutting of the ceramic tiles edges. This range offers maximum productivity, stable

Grinding Wheel Types & Different Specifications

The grinding wheel is the most essential attachment in abrasive machining, used to achieve high-precision cuts, specific geometries, and fine surface finishes. A wheel is an engineered

Contact Us

Continue your research online:

Website: <https://cgweb.co.za>

Technical inquiry: <https://cgweb.co.za/project-enquiry.html>

This document is for preliminary research. Verify specifications against current standards, product documentation and project requirements.

